

# Free-Space KD\*P Electro-Optical Modulator

(3, 8, 10mm aperture, 400nm to 2000nm)



DATASHEET

BUY NOW



## Features

- High Power Damage Threshold
- High Extinction Ratio
- Low Capacitance
- High Speed
- High Transparency
- Wide Wavelength Range

## Applications

- Q-Switch
- Phase/Power Modulation
- Pulse Picker

Made with the highest purity, strain-free, and highly deuterated KD\*P crystals, the KDPM series Pockels cells provide high optical damage resistance performance. The KDPM is packaged within ceramic housing, sapphire windows, and nitrogen-filled moisture-resistant sealings, ensuring high transmission and contrast ratios over its long lifetime. We offer three aperture sizes of 3mm, 8mm, and 10mm. The housing of the Pockels cell incorporates standard pin-type HV connectors that provide a quick connection for simplified system design and assembly. Polarization cubes can be aligned and installed at both input and output ports to form an intensity modulator.

## Specifications

Parameter	Min	Typical	Max	Unit
Wavelength Range <sup>[1]</sup>	400		600	nm
	600		900	
	900		1250	
Clear Aperture <sup>[2]</sup>	3	8	10	mm
Halfwave Voltage <sup>[3]</sup>	532nm	3300		V
	1064nm	6400		
Material Purity	99.8			%
Extinction (on/off) <sup>[4]</sup>	20		35	dB
Rise/Fall Time (10-90%)	0.5		1.1	ns
Angle Tolerance (perpendicularity)		± 0.15		Degree
Parallelism	5			"
Humidity (non-condensing)			65	%
Capacitance (dielectric constant $\epsilon \sim 13$ )		10		pF
Damage Threshold (@1064nm, 10ns, 10Hz)			10	GW/cm <sup>2</sup>
Surface Scratch/Dig		20/10		mm
Operation Temperature	10		80	°C
Electrooptic Coefficients	r41=8.8		R63=25	pm/V

### Notes:

- [1]. These are standard AR coatings, custom AR coating is available with narrower band for lower loss
- [2]. These are standard sizes, custom size is available with max length up to 25mm for lower driving voltage
- [3]. This relates to crystal size; the smaller the aperture, and the longer the length, the lower the driving voltage
- [4]. Measure at DC using two crossed polarizers

**Legal notices:** All product information is believed to be accurate and is subject to change without notice. Information contained herein shall legally bind Agiltron only if it is specifically incorporated into the terms and conditions of a sales agreement. Some specific combinations of options may not be available. The user assumes all risks and liability whatsoever in connection with the use of a product or its application.

Rev 03/14/24

© Photonwares Corporation

P +1 781-935-1200

E [sales@photonwares.com](mailto:sales@photonwares.com)

W [www.agiltron.com](http://www.agiltron.com)

Information contained herein is deemed to be reliable and accurate as of the issue date. Photonwares reserves the right to change the design or specifications at any time without notice. Agiltron is a registered trademark of Photonwares Corporation in the U.S. and other countries.

# Free-Space KD\*P Electro-Optical Modulator

(3, 8, 10mm aperture, 400nm to 2000nm)




## DATASHEET

### Warning

- Do not use it, if you are not well trained.
- Do not look at. Even indirect exposure to high power laser light can cause eye damage.
- Do not touch it. The driving high voltage can cause serious injury.
- Do not clean the optical surfaces that cause damages
- Do not solder to the crystal that causes cracks inside.

### Mechanical Drawing (mm) aperture 8mm and 10mm



\*Product dimensions may change without notice. This is sometimes required for non-standard specifications.

### Ordering Information

Prefix	Wavelength	Aperture	Length	Grade <sup>[1]</sup>	Input Cube <sup>[2]</sup>	Output Cube <sup>[2]</sup>	Mounting	Driver
KDPM-	400~600nm = 05 600~900nm = 07 900~1250nm = 10 1250~1650nm = 14	3mm=3 8mm=8 10mm= A 20mm= B	25mm=A 35mm=B 50mm=C	Standard = S Premium = P Ultra=U	No = 1 Polacore = 3 PBS = 4 Glan-Thompson=5	No = 1 Polacore = 3 PBS = 4 Glan-Thompson=5	Non=1 Yes=2	Non=0 Yes=1

[1]. Affect Intrinsic Contrast Ratio, Electro-Optic Effect Uniformity, Defect Density (related to the material selection from an as-grown crystal boule in which near center is the best)

[1]. Polacore (1060nm) – CW 10W/cm<sup>2</sup>

PBS (1060nm) – CW 15W/cm<sup>2</sup>

Glan-Thompson (1060nm) – CW 2kW/cm<sup>2</sup>


# Free-Space KD\*P Electro-Optical Modulator

(3, 8, 10mm aperture, 400nm to 2000nm)



## DATASHEET

### Modulator Half-Wave Voltage (example size)



### Application Notes (Q-switch alignment)